


**Guangzhou OTT New Materials Co., Ltd.** 

# **Foam Silicone**

#### **Product Description:**

Foam Silicone is great to make silicone foam products, such as gaskets, sheets, high temperature tubes for autoclaves, firestops, surfactants, filling materials, making foam filled applications, padding/seat cushioning, orthopedics and vibration dampening etc.





#### Appearance:

Part A: an non-toxic and odorless liquid in translucent color with platinum inside Part B: an non-toxic and odorless liquid in translucent color.

ATT: We do any curing time as you requirements



Web: www.ottsilicone.comPage 1Email: sz@ottsilicone.comTel: +86-020-86819712Email: gz@ottsilicone.com



#### **Guangzhou OTT New Materials Co., Ltd.**

#### Features:

- ♦ Amazing fluidity and easy to operate
- → Platinum-based (environmental,odorless and nontoxic)
- ♦ Mixing ration: 1:1 for easy mixing ration
- → Fast curing &de-molding
- ♦ Foam coefficient 3~6times available
- ♦ No shrink on cure
- ♦ Excellent resistance to weather, temperature, aging, acid & aging-Proofing.
- ♦ High resistance to high temperature and aging(resist -60 to 250°C)

*Model Code:* F213

#### Technical Data:

**Notes:** The data are based on the operation under room temperature of 25  $^{\circ}$ C.

Typical general characteristics	Inspection Method	Value
Product data (Catalyzed A+B)		F213
Density	Shore A	300±20
Mix Ratio	A:B	1:1
Color	1	Translucent
Pot life	25 °C (77F)	3~5mins
Curing time	25 °C (77F)	3- 5hrs
Viscosity	mPa.s	6000±2000
Foam Coefficient	times	3
Flame-retardant Leverl	/	V-1

Web: www.ottsilicone.comPage 2Email: sz@ottsilicone.com



#### **Guangzhou OTT New Materials Co., Ltd.**

#### Packing:

**Part A:** 1kg, 5kg, 20kg, 25kg, 200kg, Vacuumed Packing in white color **Part B:** 1kg, 5kg, 20kg, 25kg, 200kg, Vacuumed Packing in sky blue color





## Storage & Shelf Life:

1Year at least, stored in a cool and dry place under room temperature 25  $^{\circ}\mathrm{C}$ 

Web: www.ottsilicone.comPage 3Email: sz@ottsilicone.comTel: +86-020-86819712Email: gz@ottsilicone.com



### **Operation Method:**

By Pouring operation method into a mold or over other surfaces.



## Caution - Safety First !!!

- 1. Read the material safety data sheet(MSDS) before use.
- 2. Keep Out Of Reach Of Children.
- 3. Be careful. Use only with adequate ventilation. Contact with skin and eyes may cause irritation. Flush eyes with water for 15mins and seek immediate medical attention. Remove from skin with water-less hand cleaner followed by soap & water.



Web: www.ottsilicone.comPage 4Email: sz@ottsilicone.comTel: +86-020-86819712Email: gz@ottsilicone.com