

## Candle&Soap Molding Silicone

### ***Product Description:***

Candle&Soap Molding Silicone is good candle and Soap molding Silicone Products.

You can take it as your home hobbyists and do every design you can image. Also, you

Use it for professional candle and soap manufacture.

With good resistance to heat, deformation, acid & alkali and expansion, finished silicone molds serve very good performance in reproduction process with every fine detail on designing models.



### ***Appearance:***

Part A: **Silicone Rubber** is an white liquid

Part B: **Catalyst** is an non-toxic and odorless liquid in transparent color.

**ATT:** we can provide catalyst of Fast, Medium, Slow for hot ,cold, warm season.



**Features:** 

---

- ✧ Amazing fluidity and easy to operate
- ✧ Delicate design available
- ✧ Non Oily
- ✧ Non-toxic and odorless catalyst Provided
- ✧ Easy de-molding
- ✧ Excellent tension and tear strength
- ✧ High performance in duplication
- ✧ almost nil shrinkage below 0.2
- ✧ Excellent resistance to weather, temperature, aging, acid & aging-Proofing.

**Model Code:** S810, S815, S820, S825, 

---

**Technical Data:** 

---

**Notes:** The data are based on the operation under room temperature of 25 °C.

Typical general characteristics	Inspection Method	Value			
		S810	S815	S820	S825
Product data (Catalyzed A+B)					
Hardness	Shore A	10±2	15±2	20±2	25±2
Mix Ratio	A:B	100:3	100:3	100:3	100:3
Color	/	White	White	White	White
Pot life	25 °C (77F)	30-50mins	30-50mins	30-50mins	30-50mins
Curing time	25 °C (77F)	3- 5hrs	3- 5hrs	3- 5hrs	3- 5hrs
Viscosity	mPa.s	6000±3000	8000±3000	14000±3000	15000±3000
Tear-Strength	kN/m	≥16	≥25	≥26	≥28
Tensile -Strength	MPa	≥3.0	≥3.8	≥4.5	≥4.8
Elongation	%	≥450	≥520	≥500	≥500

Shrinkage	%	≤0.2	≤0.2	≤0.2	≤0.2
-----------	---	------	------	------	------

### **Packing:**

**Part A for silicone:** 1kg, 5kg, 20kg, 25kg, 200kg, Vacuumed Packing.

**Part B for catalyst:** 30g, 50g, 100g, 150g, 200g, 250g, 1kg.



### **Storage & Shelf Life:**

1Year at least, stored in a cool and dry place under room temperature 25℃

### **Operation Method:**

Both Pouring or brushing operation methods for our Candle&Soap Molding Silicone are available. You can chose the best one as your preference, we can provide thixotropic agent for Brushable.



### **Caution - Safety First !!!**

1. Read the material safety data sheet(MSDS) before use.
2. Keep Out Of Reach Of Children.
3. Be careful. Use only with adequate ventilation. Contact with skin and eyes may cause irritation. Flush eyes with water for 15mins and seek immediate medical attention. Remove from skin with water-less hand cleaner followed by soap & water.

